



MASTER TL-D Super 80

MASTER TL-D Super 80 18W/830 1SL/25

The MASTER TL-D Super 80 lamp offers more lumens per watt and better color rendering than TL-D standard colors. Furthermore, it has a lower mercury content. The lamp can be operated in existing TL-D luminaires.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	12000 h
Life To 50% Failures (Nom)	15000 h
Life To 50% Failures Preheat (Nom)	20000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	99 %
LSF 6000 h Rated	99 %
LSF 8000 h Rated	99 %
LSF 12000 h Rated	89 %
LSF 16000 h Rated	33 %
LSF 20000 h Rated	2 %
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux (Nom)	1350 lm
Luminous Flux (Rated) (Nom)	1350 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	440
Chromaticity Coordinate Y (Nom)	403
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Rendering Index (Nom)	85

LLMF 2000 h Rated	96 %
LLMF 4000 h Rated	95 %
LLMF 6000 h Rated	94 %
LLMF 8000 h Rated	93 %
LLMF 12000 h Rated	92 %
LLMF 16000 h Rated	91 %
LLMF 20000 h Rated	90 %
Operating and Electrical	
Power (Rated) (Nom)	18.0 W
Lamp Current (Nom)	0.360 A
Temperature	
Design Temperature (Nom)	25 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	Green Plate
Approval and Application	
Energy Efficiency Label (EEL)	A

Datasheet, 2017, January 23 data subject to change

MASTER TL-D Super 80


Mercury (Hg) Content (Nom)	2.0 mg
Energy Consumption kWh/1000 h	22 kWh
Product Data	
Full product code	871150063165740
Order product name	MASTER TL-D Super 80 18W/830 1SL/25
EAN/UPC - Product	8711500631657
Order code	927920083023

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	927920083023
Net Weight (Piece)	71.000 g
ILCOS Code	FD-18/30/1B-E-G13

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Dimensional drawing






TL-D 18W/830

Photometric data





MASTER TL-D Super 80

