Data Sheet | Item Number: 249-130

Syringe; Contents: 20 ml Alu-Plus contact paste

https://www.wago.com/249-130





Technical data

Main product function "Alu-Plus" contact paste

Material data

Fire load 0 MJ Weight 35.3 g

Commercial data	
Product Group	2 (Terminal Block Accessories)
eCl@ss 10.0	27-14-11-92
eCl@ss 9.0	27-14-11-92
ETIM 8.0	EC002848
ETIM 7.0	EC002848
PU (SPU)	20 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332133890
Customs tariff number	34039900900

Environmental Product Compliance

RoHS Compliance Status Compliant, No Exemption


Downloads

Environmental Product Compliance

Data Sheet | Item Number: 249-130

https://www.wago.com/249-130





Documentation

Bid Text			
249-130	17.05.2017	doc 23.50 KB	<u>↓</u>
249-130	19.02.2019	xml 2.49 KB	$\underline{\downarrow}$

CAD/CAE-Data

CAE data	
EPLAN Data Portal 249-130	یل
249-130	

Installation Notes

Application



WAGO Rail-Mount Terminal Blocks (up to 4 $\,\mathrm{mm^2/12}$ AWG)

For each conductor entry: Insert nozzle of the "Alu-Plus" syringe in every open conductor entry hole (one after the other).



Press plunger down until "Alu-Plus" has filled all conductor entry holes.

Application



WAGO Lighting Connectors
Push nozzle of the "Alu-Plus" syringe first
into the circular entry and then into the
square conductor entry hole of the WAGO
Lighting Connector.



Press the plunger down until "Alu-Plus" has filled both entry holes.

Note: Not suitable for higher temperature applications!


Data Sheet | Item Number: 249-130

https://www.wago.com/249-130

MAGO

Application







2. Press plunger down until "Alu-Plus" has filled all conductor entry holes.

 $\label{thm:condition} \textbf{Subject to changes. Please also observe the further product documentation!}$