

# LUXORliving D1 DALI


Item no.: 4800580



Smart Home  
Flush-mounted actuators

## Description

- Flush-mounted 1-way DALI actuator TP LUXORliving
- DALI-2 certified
- Interface between the DALI and the KNX bus system
- Simple commissioning of up to 30 ECGs in broadcast mode
- Control of RGB, RGBW, Tunable White or conventional luminaires
- DT-8 luminaire support
- Easy replacement of ECGs in the event of a fault
- Universal mounting thanks to the compact housing
- 2 binary inputs for potential-free contacts such as pushbuttons, switches, window contacts, temperature sensor (input I2)
- The binary input I1 is assigned to the output ex works (function test and operation even without programming)
- Integrated temperature monitoring for increased operational safety, e.g. in case of overload
- Download of the installation software LUXORplug at <https://luxorliving.de/luxorplug>




## Technical data

LUXORliving D1 DALI	
Operating voltage KNX	Bus voltage, $\leq 5$ mA
Operating voltage	230 V AC, 50 Hz - 60 Hz
Frequency	50 - 60 Hz
Stand-by consumption	$\pm 0.35$ W
Installation type	Flush-mounted

LUXORliving D1 DALI	
Type of connection	Terminal screws   Bus connection: KNX bus terminal
Number of channels	1
Ambient temperature	-5°C ... 45°C

## Connection example



Subject to technical changes and misprints

additional information at: [www.theben.de/product/4800580](http://www.theben.de/product/4800580)


The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.

# LUXORliving D1 DALI

Item no.: 4800580

theben

## Scale drawings



## Accessories

Temperature sensor  
Item no.: 9070321



Temperature sensor RAMSES IP  
65  
Item no.: 9070459



Flush-mounted temperature  
sensor  
Item no.: 9070496



Subject to technical changes and misprints

additional information at: [www.theben.de/product/4800580](http://www.theben.de/product/4800580)

The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.